

## Eaton 000245

Eaton Moeller® series ZW7 Current transformer-operated overload relay, 42-63A, 1N/O+1N/C

<b>PRODUCT NAME</b>	Eaton Moeller® series ZW7 Current transformer-operated overload relay
<b>CATALOG NUMBER</b>	000245
<b>PRODUCT LENGTH/DEPTH</b>	162.5 mm
<b>PRODUCT HEIGHT</b>	97 mm
<b>PRODUCT WIDTH</b>	200.5 mm
<b>PRODUCT WEIGHT</b>	0.774 kg
<b>CERTIFICATIONS</b>	CSA Class No.: 3211-03 CSA file No. 012528 IEC/EN 60947 VDE 0660 UL CSA UL 508 CSA-C22.2 No. 14 IEC/EN 60947-4-1 CE marking UL Category Control No.: NKCR UL File No.: E29184 UL Listed CSA certified

<b>CLASS</b>	Other
<b>ADJUSTABLE CURRENT RANGE - MAX</b>	63 A
<b>ADJUSTABLE CURRENT RANGE - MIN</b>	42 A
<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	1
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	1
<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	690 V
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>RESET FUNCTION</b>	Automatic Push-button
<b>MOUNTING METHOD</b>	Separate positioning

<b>CHARACTERISTIC CURVE</b>	<a href="#">eaton-tripping-devices-zw7-characteristic-curve-006.eps</a>
	<a href="#">eaton-tripping-devices-tripping-characteristic-zw7-characteristic-curve.eps</a>
	<a href="#">IL03407195Z IL04210001Z</a>
	<a href="#">eaton-tripping-devices-circuit-zw7-wiring-diagram.eps</a>
	<a href="#">eaton-tripping-devices-current-zw7-dimensions.eps</a>
	<a href="#">eaton-tripping-devices-current-zw7-dimensions-002.eps</a>
	<a href="#">eaton-tripping-devices-current-zw7-3d-drawing.eps</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

