



## Eaton 004032

Eaton Moeller® series T3 On-Off switch, 32 A, rear mounting, Basic switch, 5 contact unit(s), Contacts: 9, 45 °, Design number 15070

### □□□□

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Moeller® series T3 On-off switch |
| <b>CATALOG NUMBER</b>       | 004032                                 |
| <b>PRODUCT LENGTH/DEPTH</b> | 97 mm                                  |
| <b>PRODUCT HEIGHT</b>       | 54 mm                                  |
| <b>PRODUCT WIDTH</b>        | 61 mm                                  |
| <b>PRODUCT WEIGHT</b>       | 0.29 kg                                |
| <b>CERTIFICATIONS</b>       | CE                                     |

## □□□□

|                                                         |                                                                             |
|---------------------------------------------------------|-----------------------------------------------------------------------------|
| ACTUATOR COLOR                                          | Black                                                                       |
| RATED PERMANENT CURRENT AT AC-21, 400 V                 | 32 A                                                                        |
| RATED UNINTERRUPTED CURRENT (IU)                        | 32 A                                                                        |
| SWITCHING POWER AT 400 V                                | 15 kW                                                                       |
| RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN              | 690 V                                                                       |
| DEVICE CONSTRUCTION                                     | Built-in device fixed built-in technique                                    |
| RATED SHORT-TIME WITHSTAND CURRENT (ICW)                | 0.65 kA                                                                     |
| ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT              | Screw connection                                                            |
| ACTUATOR TYPE                                           | Short thumb-grip                                                            |
| NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)     | 0                                                                           |
| NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS) | 0                                                                           |
| RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)            | 1 kA                                                                        |
| DEGREE OF PROTECTION (FRONT SIDE)                       | IP00                                                                        |
| NUMBER OF POLES                                         | Nine-pole                                                                   |
| DEGREE OF PROTECTION                                    | NEMA Other                                                                  |
| SUITABLE FOR                                            | Ground mounting<br>Intermediate mounting<br>Distribution board installation |
| NUMBER OF SWITCHES                                      | 1                                                                           |
| NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)   | 0                                                                           |
| RATED OPERATING VOLTAGE (UE) - MAX                      | 690 V                                                                       |
| RATED OPERATING VOLTAGE (UE) - MIN                      | 690 V                                                                       |
| RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX              | 690 V                                                                       |
| RATED OPERATIONAL POWER AT AC-23A, 400 V,               | 15 kW                                                                       |

## □□

|                            |                                                                                                                                                            |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DECLARATIONS OF CONFORMITY | <a href="#">eaton-changeover-switch-declaration-of-conformity-uk251329en.pdf</a>                                                                           |
| ECAD MODEL                 | <a href="#">DA-CE-ETN.T3-5-15070_XZ</a>                                                                                                                    |
| □□□□□                      | <a href="#">IL03801006Z</a>                                                                                                                                |
| □□□                        | <a href="#">eaton-rotary-switches-t0-step-switch-wiring-diagram-206.eps</a><br><a href="#">eaton-rotary-switches-t0-step-switch-wiring-diagram-205.eps</a> |
| □□                         | <a href="#">eaton-rotary-switches-front-plate-t0-step-switch-symbol-009.eps</a>                                                                            |

|                                                      |         |
|------------------------------------------------------|---------|
| 50 HZ                                                |         |
| RATED OPERATIONAL<br>POWER AT AC-3, 380/400 V, 50 HZ |         |
|                                                      | 11 kW   |
| HOUSING COLOR                                        | Black   |
| HOUSING MATERIAL                                     | Plastic |

|  |
|--|
|  |
|  |
|  |
|  |