

Eaton 011459

Eaton Moeller® series T0 On-Off switch, 20 A, rear mounting, Basic switch, 2 contact unit(s), 3 pole, 1 N/O

PRODUCT NAME	Eaton Moeller® series T0 On-off switch
CATALOG NUMBER	011459
PRODUCT LENGTH/DEPTH	58 mm
PRODUCT HEIGHT	48 mm
PRODUCT WIDTH	48 mm
PRODUCT WEIGHT	0.088 kg
CERTIFICATIONS	CE

ACTUATOR COLOR	Black
RATED PERMANENT CURRENT AT AC-21, 400 V	20 A
RATED UNINTERRUPTED CURRENT (IU)	20 A
SWITCHING POWER AT 400 V	5.5 kW
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	690 V
DEVICE CONSTRUCTION	Built-in device fixed built-in technique
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0.32 kA
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
ACTUATOR TYPE	Short thumb-grip
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	6 kA
DEGREE OF PROTECTION (FRONT SIDE)	IP00
NUMBER OF POLES	Three-pole
DEGREE OF PROTECTION	NEMA Other
SUITABLE FOR	Ground mounting Intermediate mounting
NUMBER OF SWITCHES	1
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	1
RATED OPERATING VOLTAGE (UE) - MIN	690 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V
RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ	5.5 kW

DECLARATIONS OF CONFORMITY	eaton-step-switch-declaration-of-conformity-uk251327en.pdf
ECAD MODEL	DA-CE-ETN.T0-2-15679_XZ
	eaton-rotary-switches-switch-t0-main-switch-wiring-diagram.eps
	eaton-rotary-switches-front-plate-t0-on-off-switch-symbol-002.eps

RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	5.5 kW
HOUSING COLOR	Black
HOUSING MATERIAL	Plastic

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

