



Eaton 011736

Eaton Moeller® series T0 Changeover switch, 20 A, rear mounting, Basic switch, 2 contact unit(s), Contacts: 4, 60 °, Design number 8211

□□□□

PRODUCT NAME	Eaton Moeller® series T0 Changeover switch
CATALOG NUMBER	011736
PRODUCT LENGTH/DEPTH	58 mm
PRODUCT HEIGHT	48 mm
PRODUCT WIDTH	48 mm
PRODUCT WEIGHT	0.088 kg
CERTIFICATIONS	CE



Powering Business Worldwide

0000	
FITTED WITH:	0 (off) position
ENCLOSURE MATERIAL	Plastic
ACTUATOR TYPE	Short thumb-grip
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
NUMBER OF POLES	Two-pole
MODEL	Reverser
DEGREE OF PROTECTION (FRONT SIDE)	IP65 NEMA 12
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	11.5 A
SUITABLE FOR	Intermediate mounting Ground mounting Front mounting
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	4 kW
RATED UNINTERRUPTED CURRENT (IU)	20 A

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:

00	
DECLARATIONS OF CONFORMITY	eaton-step-switch-declaration-of-conformity-uk251327en.pdf
ECAD MODEL	DA-CE-ETN.T0-2-8211_XZ
000	eaton-rotary-switches-changeover-switch-t0-changeover-switch-wiring-diagram-002.eps
00	eaton-rotary-switches-front-plate-t0-changeover-switch-symbol-009.eps



0000 Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

