



Eaton 016424

Eaton Moeller® series T3 On-Off switch, 32 A, rear mounting, Basic switch, 1 contact unit(s), Contacts: 2, 90 °, Design number 15108

□□□□

PRODUCT NAME	Eaton Moeller® series T3 On-off switch
CATALOG NUMBER	016424
PRODUCT LENGTH/DEPTH	51 mm
PRODUCT HEIGHT	54 mm
PRODUCT WIDTH	61 mm
PRODUCT WEIGHT	0.113 kg
CERTIFICATIONS	CE

□□□□

ACTUATOR COLOR	Black
RATED PERMANENT CURRENT AT AC-21, 400 V	32 A
RATED UNINTERRUPTED CURRENT (IU)	32 A
SWITCHING POWER AT 400 V	15 kW
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	690 V
DEVICE CONSTRUCTION	Built-in device fixed built-in technique
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0.65 kA
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
ACTUATOR TYPE	Short thumb-grip
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	1 kA
DEGREE OF PROTECTION (FRONT SIDE)	IP00
NUMBER OF POLES	Two-pole
DEGREE OF PROTECTION	NEMA Other
SUITABLE FOR	Intermediate mounting Ground mounting Distribution board installation
NUMBER OF SWITCHES	1
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
RATED OPERATING VOLTAGE (UE) - MAX	690 V
RATED OPERATING VOLTAGE (UE) - MIN	690 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V
RATED OPERATIONAL POWER AT AC-23A, 400 V,	15 kW

□□

DECLARATIONS OF CONFORMITY	eaton-changeover-switch-declaration-of-conformity-uk251329en.pdf
ECAD MODEL	DA-CE-ETN.T3-1-15108_XZ
□□□□□	IL03801006Z
□□□	eaton-rotary-switches-t0-on-off-switch-wiring-diagram-015.eps eaton-rotary-switches-t0-on-off-switch-wiring-diagram-016.eps
□□	eaton-rotary-switches-front-plate-t0-changeover-switch-symbol-022.eps

50 HZ	
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	
	11 kW
HOUSING COLOR	Black
HOUSING MATERIAL	Plastic
