



Eaton 018950

Eaton Moeller® series T3 Reversing switch, 32 A, rear mounting, Basic switch, 3 contact unit(s), Contacts: 5, 45 °, Design number 2

□□□□

PRODUCT NAME	Eaton Moeller® series T3 Reversing switch
CATALOG NUMBER	018950
PRODUCT LENGTH/DEPTH	74 mm
PRODUCT HEIGHT	54 mm
PRODUCT WIDTH	61 mm
PRODUCT WEIGHT	0.195 kg
CERTIFICATIONS	CE



Powering Business Worldwide

□□□□

FEATURES	Version as reversing switch
ACTUATOR COLOR	Black
RATED PERMANENT CURRENT AT AC-21, 400 V	32 A
RATED UNINTERRUPTED CURRENT (IU)	32 A
SWITCHING POWER AT 400 V	15 kW
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	690 V
DEVICE CONSTRUCTION	Built-in device fixed built-in technique
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0.65 kA
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
ACTUATOR TYPE	Short thumb-grip
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	1 kA
DEGREE OF PROTECTION (FRONT SIDE)	IP55
NUMBER OF POLES	Five-pole
DEGREE OF PROTECTION	NEMA 12
SUITABLE FOR	Ground mounting Distribution board installation Intermediate mounting
NUMBER OF SWITCHES	1
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
RATED OPERATING VOLTAGE (UE) - MAX	690 V
RATED OPERATING VOLTAGE (UE) - MIN	690 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V

□□

DECLARATIONS OF CONFORMITY	eaton-changeover-switch-declaration-of-conformity-uk251329en.pdf
ECAD MODEL	DA-CE-ETN.T3-3-2_XZ
□□□□□	IL03801006Z
□□□	eaton-rotary-switches-t0-reversing-switch-wiring-diagram-002.eps eaton-rotary-switches-t0-reversing-switch-wiring-diagram.eps
□□	eaton-rotary-switches-front-plate-t0-changeover-switch-symbol-010.eps

