

Eaton 020271

Eaton xEnergy Safety Ci LV systems LV switchgear. Flange, knockout 6x M20, 2x M25/16, HxWxD=116x250x23mm

PRODUCT NAME	Eaton xEnergy Safety Ci flange plate
CATALOG NUMBER	020271
PRODUCT LENGTH/DEPTH	116 mm
PRODUCT HEIGHT	23 mm
PRODUCT WIDTH	142 mm
PRODUCT WEIGHT	0.14 kg
COMPLIANCES	RoHS conform

USED WITH	187.5 mm (enclosure dimensions)
	xEnergy Safety Ci Accessory for basic enclosures Basic enclosure
SPECIAL FEATURES	• Sponge-rubber, captive gasket • Quick mounting using wedge-lock fasteners (included as standard)
TYPE	• Accessory for basic enclosures • Basic enclosure • xEnergy Safety Ci
FEATURES	Pre-stamping
ACCESSORY/SPARE PART TYPE	Flanges
UNIT TYPE	Modular system
NUMBER OF CONNECTOR HOLES	0
SUITABLE FOR NOMINAL THREAD (PG) - MAX	32
SUITABLE FOR NOMINAL THREAD (PG) - MIN	16
CABLE ENTRY TYPE	6 x M20 2 x M25/16
DEGREE OF PROTECTION	Other
SURFACE PROTECTION	Untreated
SHAPE	Straight
MATERIAL	Plastic
MODEL	Cable screw gland
THREAD TYPE	Metric
THICKNESS	4 mm
SUITABLE FOR CABLE DIAMETER - MAX	0 mm
SUITABLE FOR CABLE DIAMETER - MIN	0 mm

MCAD MODEL	fl2_3.dwg fl2_3.stp
SYSTEM OVERVIEW	eaton-insulated-boards-flanges-xenergy-safety-ci-flange-plate-explosion-drawing-009.eps eaton-xeffect-ci-installation-instruction-awa31-566-z.pdf
	eaton-xenergy-safety-ci-enclosure-brochure-br014001en-en-us.pdf eaton-xenergy-safety-ci-subway-line-success-story-en-us.pdf
	eaton-xenergy-ci-safety-catalog-ca015006en-en-us.pdf
	eaton-enclosures-flanges-xeffect-ci-enclosure-dimensions.eps

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

