



Eaton 031523

Eaton xEnergy Safety Ci LV systems LV switchgear. Cable grommet, for cable D=14-54mm

□□□□

PRODUCT NAME	Eaton xEnergy Safety Ci KST enclosure accessory
CATALOG NUMBER	031523
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	65 mm
PRODUCT WIDTH	65 mm
PRODUCT WEIGHT	0.076 kg
COMPLIANCES	RoHS conform

□□□□

USED WITH

For wall thickness 2 - 3 mm
General switchboard accessory
Accessory panel building

TYPE

- Accessory panel building
- General switchboard accessory

FEATURES

Halogen free

FOR OUTER CABLE DIAMETER - MAX

54 mm

FOR OUTER CABLE DIAMETER - MIN

14 mm

FOR WALL THICKNESS - MAX

3 mm

FOR WALL THICKNESS - MIN

2 mm

NOMINAL DIAMETER

71 mm

NOMINAL SIZE (PG)

0

OPENING DIAMETER

58 mm

SEALING RANGE - MAX

54 mm

SEALING RANGE - MIN

14 mm

SURFACE FINISHING

RAL 7035, light gray

COLOR

Light gray (RAL 7035)
Gray

DEGREE OF PROTECTION

IP65

ACCESSORY/SPARE PART TYPE

Cable management

MATERIAL

Plastic
PVC

MODEL

Trimmable (cut away)

RAL-NUMBER

6008

□□

MCAD MODEL

[kt3.dwg](#) [kt3.stp](#)

□□□□

[eaton-xenergy-safety-ci-enclosure-brochure-br014001en-en-us.pdf](#)

[eaton-xenergy-safety-ci-subway-line-success-story-en-us.pdf](#)

□□□□

[eaton-xenergy-ci-safety-catalog-ca015006en-en-us.pdf](#)

□□

[eaton-insulated-boards-cable-xenergy-safety-ci-cable-grommet-dimensions.eps](#)

[eaton-distribution-boards-cable-xenergy-safety-ci-cable-grommet-3d-drawing.eps](#)

