

Eaton 082667

Eaton Moeller® series Rapid Link AS-i
branch M12

PRODUCT NAME	Eaton Rapid Link Branch
CATALOG NUMBER	082667
PRODUCT LENGTH/DEPTH	20 mm
PRODUCT HEIGHT	30.5 mm
PRODUCT WIDTH	50 mm
PRODUCT WEIGHT	0.017 kg
COMPLIANCES	CE

AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	0 °C
AMBIENT STORAGE TEMPERATURE - MAX	85 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
PRODUCT CATEGORY	AS-Interface connection and sensors
TYPE	M12 connection socket for AS-Interface connection cable
NUMBER OF POLES	Two-pole
CONTACT SURFACE MATERIAL	Other
ENCLOSURE MATERIAL	Other
CONTACT TYPE	Female
DEGREE OF PROTECTION	IP67
DEGREE OF PROTECTION (MOUNTED)	IP67
INFLAMMABILITY CLASS OF INSULATION MATERIAL (UL 94)	Other
MODEL	T-adapter

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:

- [eaton-powerxl-variable-frequency-drives-material-handling-brochure-br040017en-en-us.pdf](#)
- [eaton-rapid-link-5-brochure-br040014en-en-us.pdf](#)
- [eaton-electronics-m12-link-rapidlink-junction-dimensions.eps](#)
- [eaton-electronics-rapidlink-junction-3d-drawing.eps](#)



Eaton House
 30 Pembroke Road
 Dublin 4,
 Eaton.com
 © 2025

Follow us on social media to get the latest product and support information.