



## Eaton 100066

Eaton Moeller® series CSNS Connection cable 4 pole, DC, flat/open, 10m

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series CSNS Accessory Connection cable
<b>CATALOG NUMBER</b>	100066
<b>PRODUCT LENGTH/DEPTH</b>	25.4 mm
<b>PRODUCT HEIGHT</b>	25.4 mm
<b>PRODUCT WIDTH</b>	25.4 mm
<b>PRODUCT WEIGHT</b>	0.5 kg
<b>COMPLIANCES</b>	CE



Powering Business Worldwide

□□□□

<b>TYPE</b>	Connecting cables
<b>NUMBER OF POLES</b>	Four-pole
<b>CABLE TYPE</b>	Multi-core Cable end, open, Output side Coupling, straight, Input side
<b>CONTACT SURFACE MATERIAL</b>	Other
<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	0 V
<b>PRODUCT CATEGORY</b>	Accessories
<b>VOLTAGE TYPE</b>	DC
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>CONTINUITY RESISTOR</b>	0 mΩ
<b>NOMINAL CURRENT</b>	0 A
<b>CABLE LENGTH</b>	10 m
<b>CABLE SHEATH MATERIAL</b>	Other
<b>DEGREE OF PROTECTION</b>	Other
<b>COLOR CABLE SHEATH</b>	Yellow
<b>ELECTRICAL CONNECTION TYPE (BOX-SIDED)</b>	Other
<b>ELECTRICAL CONNECTION TYPE (FIELD-SIDED)</b>	M12
<b>CONTACT BODY MATERIAL</b>	Other
<b>PERMITTED TEMPERATURE OF OUTER CABLE (ASSEMBLED) WITHOUT VIBRATION - MAX</b>	70 °C
<b>PERMITTED TEMPERATURE OF OUTER CABLE (ASSEMBLED) WITHOUT VIBRATION - MIN</b>	40 °C
<b>PERMITTED TEMPERATURE OF OUTER CABLE (ASSEMBLING/HANDLING) - MAX</b>	70 °C
<b>PERMITTED</b>	40 °C

□□

□□□	<a href="#">eaton-proximity-switches-csns-connecting-cable-wiring-diagram.eps</a>
□□	<a href="#">eaton-proximity-switches-cds-connecting-cable-3d-drawing.eps</a>

