



Eaton 100D125R

Fuse-link, LV, 100 A, AC 500 V, D4, gR, IEC, ultra rapid

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage D fuse
CATALOG NUMBER	100D125R
PRODUCT LENGTH/DEPTH	60 mm
PRODUCT HEIGHT	33 mm
PRODUCT WIDTH	33 mm
PRODUCT WEIGHT	190 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269 EAC DIN EN 60269-3 (VDE 0636 Part 30) DIN EN 60269-1 (VDE 0636 Part 10) DIN VDE 0636-301

□□□□	
AMPERAGE RATING	100 A
FUSE SIZE	DIV
BREAKING CAPACITY	50 kA
CONSTRUCTION SIZE (FUSE INSERTS)	DIV
RATED VOLTAGE AC	500 V
CLASS	Class gR
FUSE TYPE	D125R - Ultra rapid
ACCESSORY/SPARE PART TYPE	100GD125 Red screw cap gauge piece
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
COLOR	Red
INTERRUPT RATING	50 kAIC
FUSE INDICATOR	Non-indicating
CONNECTION	Other
CONSTRUCTION	D4
CONSTRUCTION SIZE	DIV
FUSE SHAPE	Bottle
RESPONSE TIME	Ultra rapid
SUITABLE FOR	R1 1/4" / DIV Fuse base
MATERIAL	White ceramic body
RELEASE CHARACTERISTIC	Super fast (FF)
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	For domestic and general industrial applications

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:

□□	
DECLARATIONS OF CONFORMITY	eaton-low-voltage-d-fuse-declaration-of-conformity-uk251016en.pdf



□□□□
 Eaton House
 30 Pembroke Road
 Dublin 4, □□□
 Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

