



Eaton 100K07CR

Eaton Bussmann series low voltage british standard fuse, 100A, AC 600 V, DC 250 V, HRCII-C, gL/gG, CSA

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	100K07CR
UPC	051712588911
PRODUCT LENGTH/DEPTH	104 mm
PRODUCT HEIGHT	90 mm
PRODUCT WIDTH	112 mm
PRODUCT WEIGHT	53.35 g
COMPLIANCES	RoHS Compliant



Powering Business Worldwide

AMPERAGE RATING	100 A
CONSTRUCTION TYPE	HRCII-C
CURRENT TYPE	AC/DC
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	50 Hz
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	600 V
RATED VOLTAGE DC	250 V
CLASS	Class gG/gL
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	200 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	Bolt-on
CONSTRUCTION SIZE	Other
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC/DC
MATERIAL	Ceramic body
VOLTAGE RATING	600 V
TYPE	Canadian fuse
APPLICATION	Cable protection
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: