



## Eaton 100MJ25-6

Eaton Bussmann series low voltage british standard fuse, 100A, AC 415 V, V88/J, 39 x 46 mm, gU

□□□□

|                                 |                                                               |
|---------------------------------|---------------------------------------------------------------|
| <b>PRODUCT NAME</b>             | Eaton Bussmann series<br>low voltage british<br>standard fuse |
| <b>CATALOG NUMBER</b>           | 100MJ25-6                                                     |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 49 mm                                                         |
| <b>PRODUCT HEIGHT</b>           | 39 mm                                                         |
| <b>PRODUCT WIDTH</b>            | 39 mm                                                         |
| <b>PRODUCT WEIGHT</b>           | 153.7 g                                                       |
| <b>COMPLIANCES</b>              | CE Marked<br>RoHS Compliant                                   |
| <b>CERTIFICATIONS</b>           | BS<br>IEC 60269<br>EAC                                        |



Powering Business Worldwide

□□□□

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| AMPERAGE RATING                      | 100 A                                |
| FITTED WITH:                         | Slotted tags                         |
| CURRENT TYPE                         | AC                                   |
| BREAKING CAPACITY                    | 80 kA                                |
| RATED SWITCHING CAPACITY             | 80 kA                                |
| RATED VOLTAGE AC                     | 415 V                                |
| CLASS                                | Class gG/gL                          |
| FUSE TYPE                            | MJ25                                 |
| UTILIZATION CATEGORY                 | gU (utility/distribution protection) |
| COLOR                                | None                                 |
| INTERRUPT RATING                     | 80 kAIC                              |
| FUSE INDICATOR                       | None                                 |
| INSULATED METAL GRIPPING LUGS (IMGL) | No                                   |
| WATT LOSSES                          | 8.5 W                                |
| CONNECTION                           | Bolt-on                              |
| CONSTRUCTION                         | BS88/J                               |
| CONSTRUCTION SIZE                    | J                                    |
| FUSE SHAPE                           | Cylindrical                          |
| VOLTAGE TYPE                         | AC                                   |
| VOLTAGE RATING                       | 415 V                                |
| TYPE                                 | Fuse                                 |
| APPLICATION                          | feeder pillars                       |
| FUSE SYSTEM (ACCORDING TO IEC 60269) | Fuse system E                        |

□□□□:

□□□□:

□□□:

00:

00

## DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk251033en.pdf](#)