



Eaton 100NHM00B

Eaton Fuse-link, LV, 100 A, AC 500 V, NH00, aM, IEC, dual indicator, live gripping lugs

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	100NHM00B
UPC	051712233613
PRODUCT LENGTH/DEPTH	79 mm
PRODUCT HEIGHT	58 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	203 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

□□□□

AMPERAGE RATING	100 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH00
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	500 V
CLASS	Class aM
FUSE TYPE	Square body with knife blade contact
ACCESSORY/SPARE PART TYPE	SDL-00 Solid link FEH- Fuse extraction handle TD00-IP20 IP protection kit TD00-IP20I Integral protection kit TD00-IP20IC Integral Triple pole protection kit including fuse covers
UTILIZATION CATEGORY	aM (switchgear protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	5.5 W
CONNECTION	Blade end
CONSTRUCTION	NH00
CONSTRUCTION SIZE	NH00
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
SUITABLE FOR	SD00-D Single pole NH Fuse base Microswitch 170H0236 EBH Size 00 to 4 Horizontal fuse switch-disconnectors TD00-D Triple pole NH Fuse base
MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	industrial

□□

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-nh-fuse-declaration-of-conformity-uk250970en.pdf](#)

**RATED SWITCHING
CAPACITY AC**

120 kA

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

