



Eaton 102036

Eaton Distribution parts. Shunt release, up to 40A, 110-415V, 1HP

□□□□

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	102036
PRODUCT LENGTH/DEPTH	105 mm
PRODUCT HEIGHT	75.5 mm
PRODUCT WIDTH	17.7 mm
PRODUCT WEIGHT	0.11 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	North America (UL listed, CSA certified) IEC/EN 60898 CSA (Class No. 1437-01) UL 489 CSA (File No. 204453) CE marking UL (File No. E257181) CSA-C22.2 No. 5-09 UL (Category Control Number DIHS, DIHS7) EN45545-2 IEC 61373

USED WITH	Shunt releases Accessory for miniature circuit breaker Accessory
ACCESSORY/SPARE PART TYPE	Shunt release
DEGREE OF PROTECTION	IP20 (IEC) IP40 UL/CSA Type: -
FRAME	Standard front dimension: 45 mm
FREQUENCY RATING	50 Hz / 60 Hz
MOUNTING METHOD	Quick attachment with 2 latch positions for top-hat rail EN 50022 For fitting on left to: FAZ-NA, FAZ-RT
ADDITIONAL EQUIPMENT REQUIRED	Shunt release (for power circuit breaker)
TERMINAL PROTECTION	Busbar tag shroud to BGV A3
TERMINAL TYPE	Twin-purpose terminals
VOLTAGE RANGE	110 V AC - 415 V AC
AMBIENT OPERATING TEMPERATURE - MAX	75 °C
AMBIENT OPERATING TEMPERATURE - MIN	-35 °C
ASSEMBLY WIDTH	1 TE
ENCLOSURE WIDTH	105 mm
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF POLES AT MAIN CONTACT UNIT - MAX	1
NUMBER OF SWITCHES (FAULT SIGNAL)	0
VOLTAGE TYPE	AC/DC
FUNCTIONS	Shunt release (for power circuit breaker)
DEVICE FITTING	Miniature circuit breaker (MCB)

TYPE	• Accessory
	• Accessory for miniature circuit breaker
APPLICATION	Switchgear for 110-V systems
MOUNTING WIDTH	17.5 mm (1 space unit)
RATED OPERATIONAL VOLTAGE (UE) - MAX	415 V
RATED SWITCH CURRENT	0 A
SUITABLE FOR CURRENT OF MAIN CONTACT UNIT - MAX	0 A

□□□□:
□□□□:
□□□:
□□: