



□□□□□

Eaton 1036

Eaton Crouse-Hinds series throat bushing,
Rigid/IMC, Insulated, Malleable iron, 105°C,
Threaded, 2"

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series throat bushing
CATALOG NUMBER	1036
UPC	784564110367
PRODUCT LENGTH/DEPTH	2.75 in
PRODUCT HEIGHT	0.88 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	0.22 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

CONDUIT TYPE	Rigid/IMC
INSULATOR	Insulated
THREAD	Threaded
TRADE SIZE	2"
MATERIAL	Malleable iron
TEMPERATURE RATING	105°C

Links

Link	Eaton Specification Sheet - 1036
Link	Crouse-Hinds series Insulating and Throat Bushings - Rigid-IMC catalog page
Link	Insulating and Throat Bushings - Rigid-IMC UL certification
Link	Insulating and Throat Bushings - Rigid-IMC Canadian certification

Field 1
Field 2
Field 3
Field 4