



□□□□□

Eaton 1037

Eaton Crouse-Hinds series throat bushing, Rigid/IMC, Insulated, Malleable iron, 105°C, Threaded, 2-1/2"

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series throat bushing
CATALOG NUMBER	1037
UPC	784564110374
PRODUCT LENGTH/DEPTH	3.31 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	3.31 in
PRODUCT WEIGHT	0.44 lb

Certifications and compliances	
AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications	
CONDUIT TYPE	Rigid/IMC
INSULATOR	Insulated
THREAD	Threaded
TRADE SIZE	2-1/2"
MATERIAL	Malleable iron
TEMPERATURE RATING	105°C

Links	
Link 1	Eaton Specification Sheet - 1037
Link 2	Crouse-Hinds series Insulating and Throat Bushings - Rigid-IMC catalog page
Link 3	Insulating and Throat Bushings - Rigid-IMC Canadian certification
Link 4	Insulating and Throat Bushings - Rigid-IMC UL certification

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY: