

Eaton 107172

Eaton xEffect SASY 60i Enclosures Switch- & Controlgear Enclosure. Bottom plate, B=1100 mm, UL approved

PRODUCT NAME	Eaton xEffect SASY 60i terminal plate
CATALOG NUMBER	107172
PRODUCT LENGTH/DEPTH	1010 mm
PRODUCT HEIGHT	10 mm
PRODUCT WIDTH	224 mm
PRODUCT WEIGHT	0.698 kg
COMPLIANCES	UL CSA09 (refer to approbation report) CE marking IEC 60439-1 UL508A CSA-C22.2 No. 14 RoHS conform
CERTIFICATIONS	North America (UL listed, CSA certified) UL (File No. E300273) CSA (File No. 236217) CSA (Class No. 3211-37) Specially designed for North America UL (Category Control Number NMTR, NMTR7)



USED WITH	BBS-3/FL Feeder circuits BBS-3/FL-NA BBS-3/PR System for flat busbar System for profile busbars 60 mm system
SPECIAL FEATURES	For use when the air gap between the busbars and the mounting plate is not sufficient.
TYPE	
	• 60 mm system • System for flat busbar • System for profile busbars
FEATURES	Self-extinguishing acc. UL 94
ACCESSORY/SPARE PART TYPE	Bottom plate Spare part Accessory
VOLTAGE RATING (UL CSA 13)	Max. 600 V AC
DEGREE OF PROTECTION	Feeder circuits
FUNCTIONS	UL bottom plate Current limiting circuit breaker, refer to approbation report Accessory
TEMPERATURE RESISTANCE	Up to 110 °C
MATERIAL	Silicon free, chlorine free

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



[eaton-control-panels-xeffect-sasy-bottom-plate-dimensions-002.eps](#)

[eaton-control-panels-xeffect-sasy-bottom-plate-dimensions.eps](#)

[eaton-control-panels-xeffect-sasy-bottom-plate-3d-drawing.eps](#)



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

