

Eaton 107184

Eaton xEffect SASY 60i Enclosures Switch- & Controlgear Enclosure. Terminal plate, 35-120mm², 81mm

PRODUCT NAME	Eaton xEffect SASY 60i terminal plate
CATALOG NUMBER	107184
PRODUCT LENGTH/DEPTH	81 mm
PRODUCT HEIGHT	84 mm
PRODUCT WIDTH	111.76 mm
PRODUCT WEIGHT	0.52 kg
COMPLIANCES	UL CSA09 (refer to approbation report) RoHS conform
CERTIFICATIONS	CSA-C22.2 No. 14 CSA (File No. 236217) IEC 60439-1 North America (UL listed, CSA certified) CE marking UL508A UL (Category Control Number NMTR, NMTR7) UL (File No. E300273) CSA (Class No. 3211-37)

USED WITH	12 mm x 5/10 mm rail
	25 mm x 5/10 mm rail
	30 mm x 5/10 mm rail
	Double T profile
	15 mm x 5/10 mm rail
	20 mm x 5/10 mm rail
	Feeder circuits
	60 mm system
	Connection

SPECIAL FEATURES	- The terminal can be removed for the connection of uncut conductors - Looping is possible
-------------------------	---

TYPE	60 mm system - Connection
-------------	--

FEATURES	Self-extinguishing acc. UL 94
-----------------	-------------------------------

WIDTH CLAMP	81 mm
--------------------	-------

CREEPAGE RESISTANCE	CTI 200
----------------------------	---------

DEGREE OF PROTECTION	Feeder circuits UL508A; CSA-C22.2 No. 14; IEC 60439-1; CE marking
-----------------------------	---

TERMINAL CONTACT AREA	15 mm x 15 mm
------------------------------	---------------

VOLTAGE RATING (UL CSA 13)	Max. 600 V AC
-----------------------------------	---------------

BUSBAR THICKNESS - MAX	10 mm
-------------------------------	-------

BUSBAR THICKNESS - MIN	5 mm
-------------------------------	------

BUSBAR WIDTH - MAX	30 mm
---------------------------	-------

BUSBAR WIDTH - MIN	12 mm
---------------------------	-------

CONDUCTOR CROSS SECTION - MAX	120 mm ²
--------------------------------------	---------------------

RATED OPERATIONAL CURRENT (IE) - MAX	440 A
---	-------

FUNCTIONS	Connections Clamp plate Current limiting circuit breaker, refer to approbation report
------------------	---

TEMPERATURE RESISTANCE	Temperature resistant to 120 °C
-------------------------------	---------------------------------

RATED OPERATION	440 A
------------------------	-------

eaton-control-panels-xeffect-sasy-terminal-plate-dimensions-002.eps eaton-control-panels-xeffect-sasy-terminal-plate-3d-drawing-002.eps
--

CURRENT (IE)	
SUITABLE FOR	Sector conductor connection
	Flat rail
	Round conductor connection
	Three-pole
	Strip conductor connection
MATERIAL	Silicon free, chlorine free
RATED OPERATIONAL CURRENT	440 A
TERMINAL CAPACITY (CONDUCTOR)	AWG 2 - MCM 250
	16 mm x 0.8 mm (10x)
	35 mm ² - 120 mm ²

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

