



Eaton 10FC

Eaton Bussmann series high speed British standard fuse, 10A, None, Fuse

□□□□

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	10FC
UPC	051712830416
PRODUCT LENGTH/DEPTH	82 mm
PRODUCT HEIGHT	21 mm
PRODUCT WIDTH	90 mm
PRODUCT WEIGHT	8.6 g
COMPLIANCES	RoHS Compliant CE Marked

AMPERAGE RATING	10 A
BREAKING CAPACITY	90 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
RATED SWITCHING CAPACITY	90 kA
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	64 mm
MOUNTING DIMENSION	Other
CURRENT TYPE	AC
CLASS	Class aR
CLEARING (I2T)	18 at 415 V, 33 at 690 V
WATT LOSSES	3 W
FUSE SHAPE	Offset bolted tags
PRE ARC (I2T)	6
COLOR	None
CONSTRUCTION SIZE	Other
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	FC
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

DECLARATIONS OF CONFORMITY

[eaton-high-speed-british-standard-fuse-declaration-of-conformity-uk250922en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

