



## Eaton 121627

Eaton Moeller® series C22 Indicator light,  
Flat, Screw connection, Lens Red, LED Red,  
24 V AC/DC



<b>PRODUCT NAME</b>	Eaton Moeller® series C22 Indicator light
<b>CATALOG NUMBER</b>	121627
<b>PRODUCT LENGTH/DEPTH</b>	56 mm
<b>PRODUCT HEIGHT</b>	30 mm
<b>PRODUCT WIDTH</b>	30 mm
<b>PRODUCT WEIGHT</b>	0.015 kg
<b>COMPLIANCES</b>	CE Marked
<b>CERTIFICATIONS</b>	IEC 60947-5-1 CSA Std. C22.2 No. 14-05 UL 508 EN 60947-5-1 VDE UL Listed UL Category Control No.: NKCR CSA Class No.: 321103 CSA certified CSA File No.: 165628 IEC/EN 60947-5-1 CE marking CSA-C22.2 No. 14-05 and 94-M91 UL File No.: E29184 VDE 0660



Powering Business Worldwide

□□□□

<b>TYPE</b>	Indicator lights
<b>PRODUCT CATEGORY</b>	RMQ Compact
<b>VOLTAGE RATING</b>	24 Vac/dc
<b>ELECTRIC CONNECTION TYPE</b>	Screw connection
<b>FITTED WITH:</b>	Light source Front ring
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>CONNECTION TO SMARTWIRE-DT</b>	No
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4000 V AC
<b>BEZEL COLOR</b>	Other
<b>LAMP SOCKET TYPE</b>	LED
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>NUMBER OF PILOT LIGHTS</b>	1
<b>OPENING DIAMETER</b>	22.5 mm
<b>RATED INSULATION VOLTAGE (UI)</b>	250 V
<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	24 V
<b>BEZEL MATERIAL</b>	Plastic
<b>DEGREE OF PROTECTION</b>	NEMA 4X, 13 IP67/IP69K
<b>LENS COLOR</b>	Red
<b>VOLTAGE TYPE</b>	AC/DC
<b>DESIGN</b>	Flat
<b>MOUNTING POSITION</b>	As required
<b>LIGHT COLOR</b>	Red
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>	1 kA
<b>RATED OPERATIONAL VOLTAGE (UE) - MIN</b>	24 V
<b>OVERVOLTAGE CATEGORY</b>	III
<b>COLOR</b>	Red

□□

<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">eaton-pushbutton-declaration-of-conformity-uk250928en.pdf</a>
<b>ECAD MODEL</b>	<a href="#">DA-CE-ETN.C22-L-R-24</a>
<b>MCAD MODEL</b>	<a href="#">eaton-c22-l-compact-3d-model.stp</a> <a href="#">eaton-indicator-light-mcad-drawings-c22-l-compact.dwg</a>
□□□□□	<a href="#">eaton-rmq-titan-c22-pv-compact-program-emergency-buttons-instruction-leaflet-il04716025z.pdf</a>
□□□	<a href="#">eaton-operating-c22-indicator-light-wiring-diagram.eps</a>
□□	<a href="#">eaton-operating-indication-c22-indicator-light-dimensions.eps</a> <a href="#">eaton-operating-button-symbol-006.eps</a> <a href="#">eaton-operating-c22-indicator-light-3d-drawing.eps</a>

