



Eaton 121635

Eaton Moeller® series C22 Indicator light,
Flat, Screw connection, Lens white, LED
white, 120 V AC



PRODUCT NAME	Eaton Moeller® series C22 Indicator light
CATALOG NUMBER	121635
PRODUCT LENGTH/DEPTH	56 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.015 kg
CERTIFICATIONS	CSA Class No.: 321103 CSA File No.: 165628 UL 508 CSA certified UL Category Control No.: NKCR CE marking UL File No.: E29184 IEC/EN 60947-5-1 UL Listed VDE 0660 CSA-C22.2 No. 14-05 and 94-M91



Powering Business Worldwide

□□□□

TYPE	Indicator lights
PRODUCT CATEGORY	RMQ Compact
ELECTRIC CONNECTION TYPE	Screw connection
FITTED WITH:	Light source Front ring
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
BEZEL COLOR	Other
LAMP SOCKET TYPE	LED
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
NUMBER OF PILOT LIGHTS	1
OPENING DIAMETER	22.5 mm
RATED INSULATION VOLTAGE (UI)	250 V
RATED OPERATIONAL VOLTAGE (UE) - MAX	120 V
BEZEL MATERIAL	Plastic
DEGREE OF PROTECTION	NEMA 4X, 13 IP67/IP69K
LENS COLOR	White
VOLTAGE TYPE	AC
DESIGN	Flat
MOUNTING POSITION	As required
LIGHT COLOR	White
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	1 kA
RATED OPERATIONAL VOLTAGE (UE) - MIN	120 V
OVERVOLTAGE CATEGORY	III
LENS TYPE	Flat Round

□□

DECLARATIONS OF CONFORMITY	eaton-pushbutton-declaration-of-conformity-uk250928en.pdf
ECAD MODEL	DA-CE-ETN.C22-L-W-120
MCAD MODEL	eaton-c22-l-compact-3d-model.stp eaton-indicator-light-mcad-drawings-c22-l-compact.dwg
□□□□□	eaton-rmq-titan-c22-pv-compact-program-emergency-buttons-instruction-leaflet-il04716025z.pdf
□□□	eaton-operating-c22-indicator-light-wiring-diagram.eps
□□	eaton-operating-indication-c22-indicator-light-dimensions.eps eaton-operating-c22-indicator-light-3d-drawing.eps eaton-operating-button-symbol-013.eps

