

Eaton 12191130023

Eaton Crouse-Hinds series Ex-Lite ZER exit sign, 3/4" entry, Arrow downwards, 50/60 Hz, LED, Aluminum alloy, Wall mount, With nickel cadmium battery, self-diagnostic, self-test, Cover with running man and arrow 6h, 120-277 Vac, 110-250 Vdc

PRODUCT NAME	Eaton's Crouse-Hinds series Ex-Lite ZER exit sign
CATALOG NUMBER	12191130023
PRODUCT LENGTH/DEPTH	422 mm
PRODUCT HEIGHT	115 mm
PRODUCT WIDTH	230 mm
PRODUCT WEIGHT	6.7 kg

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Zone 1 Class I, Division 2 Class II, Division 2
INGRESS PROTECTION (IP) RATINGS	IP66

[Crouse-Hinds series](#)
[Global LED lighting](#)
[portfolio](#)

[Crouse-Hinds series Ex-](#)
[Lite Hazardous Area LED](#)
[Exit Signs catalog page](#)

Product specifications

LAMP TYPE	LED
VOLTAGE RATING	120-277 Vac, 110-250 Vdc
FREQUENCY RATING	50/60 Hz
MOUNTING	Wall
ENTRY SIZE	3/4"
MATERIAL	Aluminum alloy
SPECIAL FEATURES	With nickel cadmium battery, self-diagnostic, self-test

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

