



Eaton 124300

IZMX-RR24DC-40. Reset remote, 24VDC

□□□□

PRODUCT NAME	Eaton Moeller series IZMX/INX remote reset
CATALOG NUMBER	124300
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	100 mm
PRODUCT WIDTH	100 mm
PRODUCT WEIGHT	0.125 kg
COMPLIANCES	RoHS conform CE Marked



Powering Business Worldwide



USED WITH	IZMX16...F IZMX40...W IZMX16...W IZMX40...F
ELECTRIC CONNECTION TYPE	Flat plug-in connection
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	24 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	24 V
ACCESSORY/SPARE PART TYPE	Trip indication / Reset options
ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE (END VALUE) - MAX	0 A
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
INITIAL VALUE OF THE UNDELAYED SHORT-CIRCUIT RELEASE - MIN	0 A
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
VOLTAGE TYPE	DC
CONTROL VOLTAGE OPERATING RANGE	24 V DC
TYPE	Accessory



