

Eaton 124344

Eaton Moeller series IZMX/INX - ACB.
Signalling switch ON-OFF, 6W

PRODUCT NAME	Eaton Moeller series IZMX/INX auxiliary contact block
CATALOG NUMBER	124344
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	100 mm
PRODUCT WIDTH	100 mm
PRODUCT WEIGHT	0.202 kg
COMPLIANCES	RoHS conform

USED WITH	INX40... IZMX40...
ELECTRIC CONNECTION TYPE	Flat plug-in connection
RATED OPERATIONAL CURRENT (IE) AT AC-15, 220 V, 230 V, 240 V	10 A
MOUNTING METHOD	Other
ACCESSORY/SPARE PART TYPE	Auxiliary contact
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	6
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF SWITCHES (FAULT SIGNAL)	0
MODEL	Integrable
LAMP HOLDER	None
TYPE	Accessory
SPECIAL FEATURES	• 6 changeover contacts • Standard auxiliary switch for On-Off signaling. • The basic device already contains two changeover contacts. • Two additional changeover contacts possible.
RATED BREAKING CAPACITY (INDUCTIVE LOAD)	0.25 A (250 V DC) 10 A (250 V AC) 0.5 A (125 V DC)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

