



Eaton 125D200Q

Eaton Fuse-link, low voltage, 125 A, AC 500 V, D5, 56 x 46 mm, gR, DIN, IEC, fast-acting

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage D fuse
CATALOG NUMBER	125D200Q
PRODUCT LENGTH/DEPTH	258 mm
PRODUCT HEIGHT	65 mm
PRODUCT WIDTH	105 mm
PRODUCT WEIGHT	222 g
COMPLIANCES	CE RoHS Compliant CE Marked
CERTIFICATIONS	IEC/EN 60269-3 VDE 0636 IEC 60269 DIN EN 60269-3 (VDE 0636 Part 30) DIN EN 60269-1 (VDE 0636 Part 10) DIN VDE 0636-301

0000	
AMPERAGE RATING	125 A
FUSE SIZE	DV
BREAKING CAPACITY	50 kA
CONSTRUCTION SIZE (FUSE INSERTS)	DV
RATED VOLTAGE AC	500 V
CLASS	Class gR
FUSE TYPE	D200Q - Fast acting
ACCESSORY/SPARE PART TYPE	125GD200 Yellow screw cap gauge piece
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
COLOR	Yellow
INTERRUPT RATING	50 kAIC
FUSE INDICATOR	Non-indicating
CONNECTION	Other
CONSTRUCTION	D5
CONSTRUCTION SIZE	DV
FUSE SHAPE	Bottle
RESPONSE TIME	Fast-acting
SUITABLE FOR	R2/DV Fuse base
MATERIAL	White ceramic body
RELEASE CHARACTERISTIC	Fast (F)
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	For domestic and general industrial applications

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

