

Eaton 125NHG00BI

Fuse-link, LV, 125 A, AC 500 V, NH00, gL/gG, IEC, dual indicator, insulated gripping lugs

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	125NHG00BI
UPC	051712532389
PRODUCT LENGTH/DEPTH	79 mm
PRODUCT HEIGHT	58 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	203 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

AMPERAGE RATING	125 A
FITTED WITH:	Insulated metal gripping lugs
FUSE SIZE	NH00
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	500 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
ACCESSORY/SPARE PART TYPE	SDL-00 Solid link FEH- Fuse extraction handle TD00-IP20 IP protection kit TD00-IP20I Integral protection kit TD00-IP20IC Integral Triple pole protection kit including fuse covers
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	Yes
WATT LOSSES	10 W
CONNECTION	Blade end
CONSTRUCTION	NH00
CONSTRUCTION SIZE	NH00
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
SUITABLE FOR	SD00-D Single pole NH Fuse base Microswitch 170H0236 EBH Size 00 to 4 Horizontal fuse switch-disconnectors TD00-D Triple pole NH Fuse base
MATERIAL	Ceramic body

DECLARATIONS OF CONFORMITY	eaton-low-voltage-nh-fuse-declaration-of-conformity-uk250951en.pdf

QUANTITY	3
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	<ul style="list-style-type: none">• industrial• Utilities, Solar, Wind
RATED SWITCHING CAPACITY AC	120 kA

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: