



Eaton 12AKGH6B125

Air fuse-link, medium voltage, 125 A, AC 12 kV, 76 x 360 mm, back-up, BS, with striker, style 6B tags

□□□□

PRODUCT NAME	Eaton Bussmann series medium voltage BS air fuse
CATALOG NUMBER	12AKGH6B125
PRODUCT LENGTH/DEPTH	359 mm
PRODUCT HEIGHT	76.2 mm
PRODUCT WIDTH	76.2 mm
PRODUCT WEIGHT	1339.333 g
CERTIFICATIONS	BS 2692-1



Powering Business Worldwide

AMPERAGE RATING	125 A
FUSE INDICATOR	With Striker
FUSE SIZE	76 x 359 mm
BREAKING CAPACITY	20 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	British Standard
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class back-up
FUSE DIAMETER	76 mm
INTERRUPT RATING	20 kAIC
CONSTRUCTION SIZE	76 x 359 mm
MOUNTING METHOD	Clip-in
VOLTAGE RATING	12 kV
TYPE	Fuse
APPLICATION	Primary side transformer protection
FUSE TYPE	AKGH

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY: