



## Eaton 12AKGHO33X125

Air fuse-link, medium voltage, 375 A, AC 12 kV, 76 x 442 mm, back-up, BS, with striker, triple barrel

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series medium voltage BS air fuse
<b>CATALOG NUMBER</b>	12AKGHO33X125
<b>PRODUCT LENGTH/DEPTH</b>	359 mm
<b>PRODUCT HEIGHT</b>	228.6 mm
<b>PRODUCT WIDTH</b>	228.6 mm
<b>PRODUCT WEIGHT</b>	0.001 g
<b>COMPLIANCES</b>	CE



Powering Business Worldwide

□□□□

□□

<b>AMPERAGE RATING</b>	125 A
<b>FUSE INDICATOR</b>	With Striker
<b>FUSE SIZE</b>	76 x 359 mm
<b>BREAKING CAPACITY</b>	20 kA
<b>INSTALLATION TECHNIQUE</b>	Air
<b>PERFORMANCE CAT ACCORDING TO IEC 60282-1</b>	Back-up
<b>PRODUCT APPLICATION</b>	Primary side transformer protection
<b>RATED FREQUENCY - MAX</b>	50 Hz
<b>RATED FREQUENCY - MIN</b>	50 Hz
<b>RELEASE CHARACTERISTIC</b>	Other
<b>STANDARD</b>	British Standard
<b>UTILIZATION CATEGORY</b>	Other
<b>VOLTAGE TYPE</b>	AC
<b>WITH STRIKER</b>	Yes
<b>CLASS</b>	Class back-up
<b>FUSE DIAMETER</b>	76 mm
<b>INTERRUPT RATING</b>	20 kAIC
<b>CONSTRUCTION SIZE</b>	76 x 359 mm
<b>MOUNTING METHOD</b>	Clip-in
<b>VOLTAGE RATING</b>	12 kV
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	Primary side transformer protection
<b>FUSE TYPE</b>	AKGH

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

□□:



□□□□  
Eaton House  
30 Pembroke Road  
Dublin 4, □□□  
Eaton.com

© 2025 □□ □□□□□□□□

Follow us on social media to get the latest product and support information.

