



Eaton 12BDGH3620

Air fuse-link, medium voltage, 20 A, AC 12 kV, 51 x 359 mm, back-up, BS, with striker, style 36 tags

□□□□

PRODUCT NAME	Eaton Bussmann series medium voltage BS air fuse
CATALOG NUMBER	12BDGH3620
PRODUCT LENGTH/DEPTH	359 mm
PRODUCT HEIGHT	50.8 mm
PRODUCT WIDTH	50.8 mm
PRODUCT WEIGHT	2100 g
CERTIFICATIONS	BS 2692-1

□□□□	
AMPERAGE RATING	20 A
FUSE INDICATOR	With Striker
FUSE SIZE	51 x 359 mm
BREAKING CAPACITY	40 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	British Standard
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class back-up
FUSE DIAMETER	51 mm
INTERRUPT RATING	40 kAIC
CONSTRUCTION SIZE	51 x 359 mm
MOUNTING METHOD	Clip-in
VOLTAGE RATING	12 kV
TYPE	Fuse
APPLICATION	Primary side transformer protection
FUSE TYPE	BDGH

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□:

□□