

Eaton 12BDGHA10

Eaton Bussmann series medium voltage BS air fuse, 10 A, AC 12 kV, 359 x 50.8 mm, backup, BS, with striker

PRODUCT NAME	Eaton Bussmann series medium voltage BS air fuse
CATALOG NUMBER	12BDGHA10
UPC	051712240949
PRODUCT LENGTH/DEPTH	359 mm
PRODUCT HEIGHT	50.8 mm
PRODUCT WIDTH	50.8 mm
PRODUCT WEIGHT	2100 g
COMPLIANCES	BS 2692-1

AMPERAGE RATING	10 A
FUSE INDICATOR	With Striker
FUSE SIZE	51 x 359 mm
BREAKING CAPACITY	40 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	British Standard
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class back-up
BARRELS	1
CONSTRUCTION TYPE	Bolt-on
FUSE SHAPE	Cylindrical
ELEMENT	Silver
PRE ARC (I2T)	6.4 x 101
RESISTANCE	138 ohms
FUSE DIAMETER	51 mm
INTERRUPT RATING	40 kAIC
CONSTRUCTION SIZE	51 x 359 mm
MOUNTING METHOD	Clip-in
VOLTAGE RATING	12 kV
TYPE	Fuse
APPLICATION	<ul style="list-style-type: none"> • protection of primary side transformers • used in fuse switch combination units, fuse bases and fuse switches
FUSE TYPE	BDGH



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

