



## Eaton 12BFGH6B100

Eaton Bussmann series medium voltage BS air fuse, 100 A, 12 kV, 40 kA, 76 x 359 mm, With Striker

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series medium voltage BS air fuse
<b>CATALOG NUMBER</b>	12BFGH6B100
<b>UPC</b>	051712352390
<b>PRODUCT LENGTH/DEPTH</b>	359 mm
<b>PRODUCT HEIGHT</b>	76.2 mm
<b>PRODUCT WIDTH</b>	380 mm
<b>PRODUCT WEIGHT</b>	4180 g
<b>COMPLIANCES</b>	Contact factory



Powering Business Worldwide

AMPERAGE RATING	100 A
FUSE INDICATOR	With Striker
FUSE SIZE	76 x 359 mm
BREAKING CAPACITY	40 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	British Standard
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class back-up
CONSTRUCTION TYPE	Bolt-on
FUSE SHAPE	Cylindrical, offset bolted tags
FUSE DIAMETER	76 mm
INTERRUPT RATING	40 kAIC
CONSTRUCTION SIZE	76 x 359 mm
MOUNTING METHOD	Clip-in
PACKAGING TYPE	Standard
VOLTAGE RATING	12 kV
TYPE	Fuse

## APPLICATION

- protection of  
primary side  
transformers
- used in fuse switch  
combination units,  
fuse bases and  
fuse switches

## FUSE TYPE

BFGH

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

