



## Eaton 12BFGHF100

Eaton Bussmann series medium voltage BS air fuse, 12 kV, 100 A, 40 kA, 76 x 461 mm, With Striker

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series medium voltage BS air fuse
<b>CATALOG NUMBER</b>	12BFGHF100
<b>PRODUCT LENGTH/DEPTH</b>	461 mm
<b>PRODUCT HEIGHT</b>	76 mm
<b>PRODUCT WIDTH</b>	76 mm
<b>PRODUCT WEIGHT</b>	4200 g
<b>COMPLIANCES</b>	BS 2692-1
<b>CERTIFICATIONS</b>	KEMA Certified ASTA

USED WITH	A3354730 Fuse clip
AMPERAGE RATING	100 A
FUSE INDICATOR	With Striker
FUSE SIZE	76 x 461 mm
BREAKING CAPACITY	40 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	British Standard
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class back-up
PRE ARC (I2T)	1.1 x 103
RESISTANCE	6.88 ohms
FUSE DIAMETER	76 mm
INTERRUPT RATING	40 kAIC
CONSTRUCTION SIZE	76 x 461 mm
MOUNTING METHOD	Clip-in
VOLTAGE RATING	12 kV
TYPE	Fuse

APPLICATION	<ul style="list-style-type: none"> <li>• protection of primary side transformers</li> <li>• used in fuse switch combination units, fuse bases and fuse switches</li> </ul>
-------------	--

FUSE TYPE	BFGH
-----------	------

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

