



Eaton 12FDLSJ10

Eaton Bussmann series medium voltage DIN fuse, 10 A, AC 12 kV, 2", 51 x 292 mm, fullrange, DIN, with striker

□□□□

PRODUCT NAME	Eaton Bussmann series medium voltage DIN fuse
CATALOG NUMBER	12FDLSJ10
UPC	051712664523
PRODUCT LENGTH/DEPTH	292 mm
PRODUCT HEIGHT	51 mm
PRODUCT WIDTH	51 mm
PRODUCT WEIGHT	1630 g
COMPLIANCES	DIN 43625 VDE 0670-4 IEC 60282-1
CERTIFICATIONS	IEC Rated

USED WITH	270303 Fuse clip A3354710 Fuse clip
AMPERAGE RATING	10 A
FUSE INDICATOR	With Striker
FUSE SIZE	51 x 292 mm
BREAKING CAPACITY	50 kA
INSTALLATION TECHNIQUE	Air
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Full-range
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	50 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	DIN
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
CLASS	Class full-range
BARRELS	1
CONSTRUCTION TYPE	Bolt-on
ELEMENT	Silver
RESISTANCE	116 Ohms
WATT LOSSES	15 W
FUSE DIAMETER	51 mm
INTERRUPT RATING	50 kAIC
CONSTRUCTION SIZE	51 x 292 mm
PACKAGING TYPE	Standard
VOLTAGE RATING	12 kV
TYPE	Fuse
APPLICATION	• transformer protection • indoor or outdoor use
FUSE TYPE	FDLSJ

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

