



## Eaton 12OHFMA100

Oil fuse-link, medium voltage, 100 A, AC 12 kV, BS2692 F01, 254 x 63.5 mm, back-up, BS, IEC, ESI, with striker

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series medium voltage oil fuse
<b>CATALOG NUMBER</b>	12OHFMA100
<b>UPC</b>	051712534147
<b>PRODUCT LENGTH/DEPTH</b>	254 mm
<b>PRODUCT HEIGHT</b>	63.5 mm
<b>PRODUCT WIDTH</b>	63.5 mm
<b>PRODUCT WEIGHT</b>	1900 g
<b>COMPLIANCES</b>	BS 2692-1 ESI 12-8
<b>CERTIFICATIONS</b>	IEC Rated IEC60282-1



Powering Business Worldwide

<b>AMPERAGE RATING</b>	100 A
<b>FUSE INDICATOR</b>	with striker
<b>FUSE SIZE</b>	254 x 63.5 mm
<b>BREAKING CAPACITY</b>	40 kA
<b>INSTALLATION TECHNIQUE</b>	Oil
<b>PERFORMANCE CAT ACCORDING TO IEC 60282-1</b>	Back-up
<b>PRODUCT APPLICATION</b>	Primary side transformer protection
<b>RATED FREQUENCY - MAX</b>	60 Hz
<b>RATED FREQUENCY - MIN</b>	50 Hz
<b>RELEASE CHARACTERISTIC</b>	Other
<b>STANDARD</b>	British Standard
<b>UTILIZATION CATEGORY</b>	Other
<b>VOLTAGE TYPE</b>	AC
<b>WITH STRIKER</b>	Yes
<b>FUSE DIAMETER</b>	63.5 mm
<b>CLASS</b>	Class back-up
<b>CONSTRUCTION TYPE</b>	F01/BS 2692
<b>FUSE SHAPE</b>	Cylindrical
<b>INTERRUPT RATING</b>	40 kAIC 45 kAIC
<b>CONSTRUCTION SIZE</b>	63.5 x 254 mm
<b>VOLTAGE RATING</b>	12 kV
<b>TYPE</b>	fuse
<b>APPLICATION</b>	protection of primary side transformer, and oil-filled fuse switch combination unit
<b>FUSE TYPE</b>	OHFM

