

Eaton 12OHFMA71

Oil fuse-link, medium voltage, 71 A, AC 12 kV, BS2692 F01, 254 x 63.5 mm, back-up, BS, IEC, ESI, with striker

PRODUCT NAME	Eaton Bussmann series medium voltage oil fuse
CATALOG NUMBER	12OHFMA71
UPC	051712585477
PRODUCT LENGTH/DEPTH	254 mm
PRODUCT HEIGHT	63.5 mm
PRODUCT WIDTH	63.5 mm
PRODUCT WEIGHT	1900 g
COMPLIANCES	BS 2692-1 ESI 12-8
CERTIFICATIONS	IEC Rated IEC60282-1

AMPERAGE RATING	71 A
FUSE INDICATOR	with striker
FUSE SIZE	254 x 63.5 mm
BREAKING CAPACITY	45 kA
INSTALLATION TECHNIQUE	Oil
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	60 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	British Standard
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
FUSE DIAMETER	63.5 mm
JOULE INTEGRAL (I2T) - MAX OPERATING	5.4 x 104
JOULE INTEGRAL (I2T) - MIN PRE-ARCING	3.2 x 103
RESISTANCE	12.3
CLASS	Class back-up
BARRELS	1
CONSTRUCTION TYPE	F01/BS 2692
FUSE SHAPE	Cylindrical
INTERRUPT RATING	40 kAIC 45 kAIC
CONSTRUCTION SIZE	63.5 x 254 mm
VOLTAGE RATING	12 kV
TYPE	fuse
APPLICATION	protection of primary side transformer, and oil-filled fuse switch combination unit
FUSE TYPE	OHFM



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

