



Eaton 135198

Eaton CR Installation contactor, 25A, 24V AC, 4NO

□□□□

PRODUCT NAME	Eaton CR contactor
CATALOG NUMBER	135198
PRODUCT LENGTH/DEPTH	75 mm
PRODUCT HEIGHT	80 mm
PRODUCT WIDTH	36 mm
PRODUCT WEIGHT	0.244 kg
COMPLIANCES	RoHS conform

□□□□

AMPERAGE RATING	25 A
FEATURES	Additional equipment possible
DEGREE OF PROTECTION	IP20
INCANDESCENT LAMP LOAD - MAX	2200 W
LOAD FLUORESCENT LAMP - MAX	1200 VA
LOAD FLUORESCENT LAMP (DUO CIRCUIT) - MAX	1440 VA
LOAD FLUORESCENT LAMP (PARALLEL COMPENSATED) - MAX	400 VA
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	4
NUMBER OF MODULAR SPACINGS	2
RATED OPERATING VOLTAGE (UE) - MAX	400 V
RATED OPERATING VOLTAGE (UE) - MIN	400 V
UTILITY CATEGORY	1
VOLTAGE RATING (EXCITATION) - MAX	26.4 V
VOLTAGE RATING (EXCITATION) - MIN	20.4 V
BUILT-IN DEPTH	60 mm
VOLTAGE TYPE	AC
UTILIZATION CATEGORY (ACCORDING TO EN IEC 60947-4-1)	AC-1

□□

