

Eaton 136263

Eaton Moeller® series CSAR Connection cable, 3p, AC, coupling m12 angled, open end, L=5m

PRODUCT NAME	Eaton Moeller® series CSAR Accessory Connection cable
CATALOG NUMBER	136263
PRODUCT LENGTH/DEPTH	165.1 mm
PRODUCT HEIGHT	12.7 mm
PRODUCT WIDTH	165.1 mm
PRODUCT WEIGHT	0.09 kg
CERTIFICATIONS	CE



TYPE	Connecting cables
NUMBER OF POLES	Three-pole
CABLE TYPE	Multi-core Cable end, open, Output side Coupling, angled, Input side
CONTACT SURFACE MATERIAL	Other
RATED OPERATIONAL VOLTAGE (UE) - MAX	0 V
PRODUCT CATEGORY	Accessories
VOLTAGE TYPE	AC
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
CONTINUITY RESISTOR	0 mΩ
NOMINAL CURRENT	0 A
CABLE LENGTH	5 m
CABLE SHEATH MATERIAL	Other
DEGREE OF PROTECTION	Other
COLOR CABLE SHEATH	Yellow
ELECTRICAL CONNECTION TYPE (BOX-SIDED)	Other
ELECTRICAL CONNECTION TYPE (FIELD-SIDED)	M12
CONTACT BODY MATERIAL	Other
PERMITTED TEMPERATURE OF OUTER CABLE (ASSEMBLED) WITHOUT VIBRATION - MAX	70 °C
PERMITTED TEMPERATURE OF OUTER CABLE (ASSEMBLED) WITHOUT VIBRATION - MIN	40 °C
PERMITTED TEMPERATURE OF OUTER CABLE (ASSEMBLING/HANDLING)	70 °C



eaton-proximity-switches-csas-connecting-cable-wiring-diagram.eps
eaton-proximity-switches-csdr-connecting-cable-3d-drawing.eps

- MAX	
PERMITTED TEMPERATURE OF OUTER CABLE (ASSEMBLING/HANDLING)	40 °C
- MIN	
PLUG-IN CONTACT TYPE (BOX-SIDED)	Male (plug)
PLUG-IN CONTACT TYPE (FIELD-SIDED)	Female (bus)
POSITIONING CABLE FEED (BOX-SIDED)	Other
POSITIONING CABLE FEED (FIELD-SIDED)	Angled

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

