



Eaton 136316

Eaton Moeller® series CSDS Connection cable, 4p, DC current, coupling M12 flat, plug M12 flat, L=1.5m

□□□□

PRODUCT NAME	Eaton Moeller® series CSDS Accessory Connection cable
CATALOG NUMBER	136316
PRODUCT LENGTH/DEPTH	177.79 mm
PRODUCT HEIGHT	25.39 mm
PRODUCT WIDTH	152.39 mm
PRODUCT WEIGHT	0.27 kg
CERTIFICATIONS	CE



Powering Business Worldwide

□□□□

TYPE	Connecting cables
NUMBER OF POLES	Four-pole
CABLE TYPE	Plug, straight, Output side Multi-core Coupling, straight, Input side
CONTACT SURFACE MATERIAL	Other
PRODUCT CATEGORY	Accessories
VOLTAGE TYPE	DC
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
CABLE LENGTH	1.5 m
CABLE SHEATH MATERIAL	Other
DEGREE OF PROTECTION	Other
COLOR CABLE SHEATH	Yellow
ELECTRICAL CONNECTION TYPE (BOX-SIDED)	M12
ELECTRICAL CONNECTION TYPE (FIELD-SIDED)	M12
CONTACT BODY MATERIAL	Other
PERMITTED TEMPERATURE OF OUTER CABLE (ASSEMBLED) WITHOUT VIBRATION - MAX	70 °C
PERMITTED TEMPERATURE OF OUTER CABLE (ASSEMBLED) WITHOUT VIBRATION - MIN	40 °C
PERMITTED TEMPERATURE OF OUTER CABLE (ASSEMBLING/HANDLING) - MAX	70 °C
PERMITTED TEMPERATURE OF OUTER CABLE (ASSEMBLING/HANDLING) - MIN	40 °C
PLUG-IN CONTACT TYPE	Male (plug)

□□

□□□	eaton-proximity-switches-csdr-connecting-cable-wiring-diagram-003.eps
□□	eaton-proximity-switches-csds-connecting-cable-3d-drawing-002.eps

