



□□□□

Eaton 15.5OEFMA50

Oil fuse-link, medium voltage, 50 A, AC 15.5 kV, BS2692 F01, 63.5 x 254 mm, back-up, BS, IEC, ESI, with striker

□□□□

PRODUCT NAME	Eaton Bussmann series medium voltage oil fuse
CATALOG NUMBER	15.5OEFMA50
UPC	051712279796
PRODUCT LENGTH/DEPTH	254 mm
PRODUCT HEIGHT	63.5 mm
PRODUCT WIDTH	63.5 mm
PRODUCT WEIGHT	1900 g
COMPLIANCES	BS 2692-1 ESI 12-8
CERTIFICATIONS	IEC Rated IEC60282-1



Powering Business Worldwide

AMPERAGE RATING	50 A
FUSE INDICATOR	with striker
FUSE SIZE	254 x 63.5 mm
BREAKING CAPACITY	40 kA
INSTALLATION TECHNIQUE	Oil
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
PRODUCT APPLICATION	Primary side transformer protection
RATED FREQUENCY - MAX	60 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	Other
STANDARD	British Standard
UTILIZATION CATEGORY	Other
VOLTAGE TYPE	AC
WITH STRIKER	Yes
FUSE DIAMETER	63.5 mm
JOULE INTEGRAL (I²T) - MAX OPERATING	3 x 10 ⁴
JOULE INTEGRAL (I²T) - MIN PRE-ARCING	3.3 x 10 ³
RESISTANCE	22.1
CLASS	Class back-up
CONSTRUCTION TYPE	F01/BS 2692
FUSE SHAPE	Cylindrical
INTERRUPT RATING	40 kAIC
CONSTRUCTION SIZE	63.5 x 254 mm
VOLTAGE RATING	15.5 kV
TYPE	fuse
APPLICATION	protection of primary side transformer, and oil-filled fuse switch combination unit
FUSE TYPE	OEFM

