



Eaton 158728

Eaton Distribution parts. Fuse switch
disconnecter, 3p, NH1, AC22, 35C101CCAE

□□□□

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	158728
PRODUCT LENGTH/DEPTH	590 mm
PRODUCT HEIGHT	74.5 mm
PRODUCT WIDTH	280 mm
PRODUCT WEIGHT	7.101 kg
COMPLIANCES	RoHS conform



Powering Business Worldwide

□□□□

□□

FEATURES	Motor drive optional
----------	----------------------

FITTED WITH:	Error protection Connectors
--------------	--------------------------------

RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ	0 kW
---	------

RATED PERMANENT CURRENT (IU)	250 A
---------------------------------	-------

RATED UNINTERRUPTED CURRENT (IU)	250 A
-------------------------------------	-------

CONDITIONED RATED SHORT-CIRCUIT CURRENT IQ	55 kA
--	-------

WITH ERROR PROTECTION	Yes
--------------------------	-----

NUMBER OF POLES	Three-pole
-----------------	------------

RATED OPERATION POWER AT AC-23, 400 V	0 kW
--	------

RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0 kA
--	------

ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
--	------------------

ACTUATOR POSITION	Front side
-------------------	------------

ACTUATOR TYPE	Long turning handle
---------------	---------------------

SUITABLE FOR	Front mounting
--------------	----------------

RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	55 kA
--	-------

SUITABLE FOR FUSES	NH1
--------------------	-----

CABLE ENTRY TYPE	Side
------------------	------

DEGREE OF PROTECTION (FRONT SIDE)	IP40
--------------------------------------	------

POWER RATING AT AC-23, 400 V	0 kW
---------------------------------	------

RATED OPERATING VOLTAGE (UE) AT AC - MAX	690 V
--	-------

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

