



## Eaton 159613

Eaton Distribution parts. Fuse switch  
disconnecter, 3p, NH1, AC23, 35C105CC

### □□□□

<b>PRODUCT NAME</b>	Eaton Distribution parts
<b>CATALOG NUMBER</b>	159613
<b>PRODUCT LENGTH/DEPTH</b>	590 mm
<b>PRODUCT HEIGHT</b>	74.5 mm
<b>PRODUCT WIDTH</b>	280 mm
<b>PRODUCT WEIGHT</b>	6.947 kg
<b>COMPLIANCES</b>	RoHS conform



*Powering Business Worldwide*

FEATURES	Motor drive optional
FITTED WITH:	Connectors Error protection
RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ	0 kW
RATED PERMANENT CURRENT (IU)	250 A
RATED UNINTERRUPTED CURRENT (IU)	250 A
CONDITIONED RATED SHORT-CIRCUIT CURRENT IQ	100 kA
WITH ERROR PROTECTION	Yes
NUMBER OF POLES	Three-pole
RATED OPERATION POWER AT AC-23, 400 V	0 kW
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0 kA
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
ACTUATOR POSITION	Front side
ACTUATOR TYPE	Long turning handle
SUITABLE FOR	Front mounting
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	80 kA 100 kA
SUITABLE FOR FUSES	NH1
CABLE ENTRY TYPE	Side
DEGREE OF PROTECTION (FRONT SIDE)	IP40
POWER RATING AT AC-23, 400 V	0 kW
RATED OPERATING VOLTAGE (UE) AT AC - MAX	690 V

