



Eaton 159624

Eaton Distribution parts. Fuse switch
disconnecter, 3p, NH1, AC23, 35BC105CCAE

□□□□

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	159624
PRODUCT LENGTH/DEPTH	590 mm
PRODUCT HEIGHT	74.5 mm
PRODUCT WIDTH	280 mm
PRODUCT WEIGHT	7.101 kg
COMPLIANCES	RoHS conform

FEATURES Motor drive optional

FITTED WITH: Error protection
Connectors

**RATED OPERATIONAL
POWER AT AC-23A, 400 V,
50 HZ** 0 kW

**RATED PERMANENT
CURRENT (IU)** 250 A

**RATED UNINTERRUPTED
CURRENT (IU)** 250 A

**CONDITIONED RATED
SHORT-CIRCUIT CURRENT
IQ** 100 kA

**WITH ERROR
PROTECTION** Yes

NUMBER OF POLES Three-pole

**RATED OPERATION
POWER AT AC-23, 400 V** 0 kW

**RATED SHORT-TIME
WITHSTAND CURRENT
(ICW)** 0 kA

**ELECTRICAL
CONNECTION TYPE OF
MAIN CIRCUIT** Screw connection

ACTUATOR POSITION Front side

ACTUATOR TYPE Long turning handle

SUITABLE FOR Front mounting

**RATED CONDITIONAL
SHORT-CIRCUIT CURRENT
(IQ)** 100 kA

SUITABLE FOR FUSES NH1

CABLE ENTRY TYPE Side

**DEGREE OF PROTECTION
(FRONT SIDE)** IP40

**POWER RATING AT AC-23,
400 V** 0 kW

**RATED OPERATING
VOLTAGE (UE) AT AC -
MAX** 690 V

