



Eaton 15KBR40

Expulsion fuse-link, medium voltage, 40 A, AC 15 kV, 533 mm, ANSI, K fast, style BR termination

□□□□

PRODUCT NAME	Eaton Bussmann series medium voltage expulsion fuse
CATALOG NUMBER	15KBR40
UPC	051712519359
PRODUCT LENGTH/DEPTH	225 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	106 mm
PRODUCT WEIGHT	46.24 g
COMPLIANCES	ANSI C37.42



Powering Business Worldwide

0000	
AMPERAGE RATING	40 A
CURRENT CHARACTERISTIC TYPE	Type K - Complies with ANSI C 37-42 requirements for fast acting K Characteristics
RATED FREQUENCY - MAX	60 Hz
RATED FREQUENCY - MIN	50 Hz
RELEASE CHARACTERISTIC	K
STANDARD	ANSI
TYPE OF TERMINATION	Removable buttonhead
VOLTAGE TYPE	AC
COLOR	Yellow
INTERRUPT RATING	8 kAIC
CONSTRUCTION SIZE	533 mm
VOLTAGE RATING	15 kV
TYPE	Medium Voltage Expulsion Fuse Link
APPLICATION	Primary side transformer protection, feeder protection, capacitor bank protection

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

