



Eaton 160993

Eaton Distribution parts. Fuse switch
disconnector, 3p, NH2, AC23, 35C401CC

XXXX

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	160993
PRODUCT LENGTH/DEPTH	590 mm
PRODUCT HEIGHT	149.5 mm
PRODUCT WIDTH	280 mm
PRODUCT WEIGHT	14.308 kg
COMPLIANCES	RoHS conform

0000

00

FEATURES	Motor drive optional
FITTED WITH:	Connectors Error protection
RATED OPERATIONAL	
POWER AT AC-23A, 400 V, 50 Hz	0 kW
RATED PERMANENT CURRENT (IU)	400 A
RATED UNINTERRUPTED CURRENT (IU)	400 A
CONDITIONED RATED SHORT-CIRCUIT CURRENT (IQ)	100 kA
WITH ERROR PROTECTION	Yes
NUMBER OF POLES	Three-pole
RATED OPERATION POWER AT AC-23, 400 V	0 kW
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0 kA
ELECTRICAL	
CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
ACTUATOR POSITION	Front side
ACTUATOR TYPE	Long turning handle
SUITABLE FOR	Front mounting
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	100 kA
SUITABLE FOR FUSES	NH2
CABLE ENTRY TYPE	Side
DEGREE OF PROTECTION (FRONT SIDE)	IP40
POWER RATING AT AC-23, 400 V	0 kW
RATED OPERATING VOLTAGE (UE) AT AC - MAX	690 V

□□□□:

□□□□⋮

10

10

EATON
Powering Business Worldwide

□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2026

A horizontal row of 20 empty square boxes for writing names.

