

# Eaton 161101

Eaton Distribution parts. Fuse switch disconnecter, 3p, NH2, AC23, 35C205CC

<b>PRODUCT NAME</b>	Eaton Distribution parts
<b>CATALOG NUMBER</b>	161101
<b>PRODUCT LENGTH/DEPTH</b>	590 mm
<b>PRODUCT HEIGHT</b>	149.5 mm
<b>PRODUCT WIDTH</b>	280 mm
<b>PRODUCT WEIGHT</b>	14.308 kg
<b>COMPLIANCES</b>	RoHS conform



<b>FEATURES</b>	Motor drive optional
<b>FITTED WITH:</b>	Connectors Error protection
<b>RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ</b>	0 kW
<b>RATED PERMANENT CURRENT (IU)</b>	400 A
<b>RATED UNINTERRUPTED CURRENT (IU)</b>	400 A
<b>CONDITIONED RATED SHORT-CIRCUIT CURRENT IQ</b>	100 kA
<b>WITH ERROR PROTECTION</b>	Yes
<b>NUMBER OF POLES</b>	Three-pole
<b>RATED OPERATION POWER AT AC-23, 400 V</b>	0 kW
<b>RATED SHORT-TIME WITHSTAND CURRENT (ICW)</b>	0 kA
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>ACTUATOR POSITION</b>	Front side
<b>ACTUATOR TYPE</b>	Long turning handle
<b>SUITABLE FOR</b>	Front mounting
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>	100 kA
<b>SUITABLE FOR FUSES</b>	NH2
<b>CABLE ENTRY TYPE</b>	Side
<b>DEGREE OF PROTECTION (FRONT SIDE)</b>	IP40
<b>POWER RATING AT AC-23, 400 V</b>	0 kW
<b>RATED OPERATING VOLTAGE (UE) AT AC - MAX</b>	690 V

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

:

---



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

