



□□□□

Eaton 162297

Eaton Distribution parts. Fuse switch
disconnecter, 4p, NH3, AC22, 11C605BMC

□□□□

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	162297
PRODUCT LENGTH/DEPTH	590 mm
PRODUCT HEIGHT	299.5 mm
PRODUCT WIDTH	280 mm
PRODUCT WEIGHT	23.884 kg
COMPLIANCES	RoHS conform



Powering Business Worldwide



FEATURES	Motor drive optional
FITTED WITH:	Connectors Error protection
RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ	0 kW
RATED PERMANENT CURRENT (IU)	630 A
RATED UNINTERRUPTED CURRENT (IU)	630 A
CONDITIONED RATED SHORT-CIRCUIT CURRENT IQ	55 kA
NUMBER OF POLES	Four-pole
RATED OPERATION POWER AT AC-23, 400 V	0 kW
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0 kA
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
ACTUATOR POSITION	Front side
ACTUATOR TYPE	Long turning handle
SUITABLE FOR	Busbar mounting Front mounting
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	55 kA
SUITABLE FOR FUSES	NH3
CABLE ENTRY TYPE	Side
DEGREE OF PROTECTION (FRONT SIDE)	IP40
POWER RATING AT AC-23, 400 V	0 kW
RATED OPERATING VOLTAGE (UE) AT AC - MAX	690 V



