



Eaton 163464

Eaton Distribution parts. Fuse switch
disconnecter, 3p, NH00, AC22, 35C101BMC

□□□□

| | |
|-----------------------------|--------------------------|
| PRODUCT NAME | Eaton Distribution parts |
| CATALOG NUMBER | 163464 |
| PRODUCT LENGTH/DEPTH | 590 mm |
| PRODUCT HEIGHT | 49.5 mm |
| PRODUCT WIDTH | 280 mm |
| PRODUCT WEIGHT | 5.162 kg |
| COMPLIANCES | RoHS conform |



Powering Business Worldwide



| | |
|--|--------------------------------|
| FEATURES | Motor drive optional |
| FITTED WITH: | Connectors Error protection |
| RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ | 0 kW |
| RATED PERMANENT CURRENT (IU) | 160 A |
| RATED UNINTERRUPTED CURRENT (IU) | 160 A |
| CONDITIONED RATED SHORT-CIRCUIT CURRENT IQ | 55 kA |
| WITH ERROR PROTECTION | Yes |
| NUMBER OF POLES | Three-pole |
| RATED OPERATION POWER AT AC-23, 400 V | 0 kW |
| RATED SHORT-TIME WITHSTAND CURRENT (ICW) | 0 kA |
| ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT | Screw connection |
| ACTUATOR POSITION | Front side |
| ACTUATOR TYPE | Long turning handle |
| SUITABLE FOR | Front mounting |
| RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ) | 55 kA |
| SUITABLE FOR FUSES | NH00 |
| CABLE ENTRY TYPE | Side |
| DEGREE OF PROTECTION (FRONT SIDE) | IP40 |
| POWER RATING AT AC-23, 400 V | 0 kW |
| RATED OPERATING VOLTAGE (UE) AT AC - MAX | 690 V |

