



□□□□□

## Eaton 163798

Eaton Distribution parts. Fuse switch  
disconnecter, 4p, NH00, AC22, 35C155BMCE

□□□□

|                         |                          |
|-------------------------|--------------------------|
| PRODUCT NAME            | Eaton Distribution parts |
| CATALOG NUMBER          | 163798                   |
| PRODUCT<br>LENGTH/DEPTH | 590 mm                   |
| PRODUCT HEIGHT          | 99.5 mm                  |
| PRODUCT WIDTH           | 280 mm                   |
| PRODUCT WEIGHT          | 8.738 kg                 |
| COMPLIANCES             | RoHS conform             |



Powering Business Worldwide

|                                                       |                                   |
|-------------------------------------------------------|-----------------------------------|
| FEATURES                                              | Motor drive optional              |
| FITTED WITH:                                          | Connectors<br>Error protection    |
| RATED OPERATIONAL<br>POWER AT AC-23A, 400 V,<br>50 HZ | 0 kW                              |
| RATED PERMANENT<br>CURRENT (IU)                       | 160 A                             |
| RATED UNINTERRUPTED<br>CURRENT (IU)                   | 160 A                             |
| CONDITIONED RATED<br>SHORT-CIRCUIT CURRENT<br>IQ      | 55 kA                             |
| NUMBER OF POLES                                       | Four-pole                         |
| RATED OPERATION<br>POWER AT AC-23, 400 V              | 0 kW                              |
| RATED SHORT-TIME<br>WITHSTAND CURRENT<br>(ICW)        | 0 kA                              |
| ELECTRICAL<br>CONNECTION TYPE OF<br>MAIN CIRCUIT      | Screw connection                  |
| ACTUATOR POSITION                                     | Front side                        |
| ACTUATOR TYPE                                         | Long turning handle               |
| SUITABLE FOR                                          | Busbar mounting<br>Front mounting |
| RATED CONDITIONAL<br>SHORT-CIRCUIT CURRENT<br>(IQ)    | 55 kA                             |
| SUITABLE FOR FUSES                                    | NH00                              |
| CABLE ENTRY TYPE                                      | Side                              |
| DEGREE OF PROTECTION<br>(FRONT SIDE)                  | IP40                              |
| POWER RATING AT AC-23,<br>400 V                       | 0 kW                              |
| RATED OPERATING<br>VOLTAGE (UE) AT AC -<br>MAX        | 690 V                             |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
|                 |



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

