



## Eaton 163876

Eaton Distribution parts. Fuse switch  
disconnecter, 3p, NH00, AC23, 31C071CC

### □□□□

|                             |                          |
|-----------------------------|--------------------------|
| <b>PRODUCT NAME</b>         | Eaton Distribution parts |
| <b>CATALOG NUMBER</b>       | 163876                   |
| <b>PRODUCT LENGTH/DEPTH</b> | 590 mm                   |
| <b>PRODUCT HEIGHT</b>       | 49.5 mm                  |
| <b>PRODUCT WIDTH</b>        | 280 mm                   |
| <b>PRODUCT WEIGHT</b>       | 5.059 kg                 |
| <b>COMPLIANCES</b>          | RoHS conform             |

|                                                       |                                |
|-------------------------------------------------------|--------------------------------|
| FEATURES                                              | Motor drive optional           |
| FITTED WITH:                                          | Connectors<br>Error protection |
| RATED OPERATIONAL<br>POWER AT AC-23A, 400 V,<br>50 HZ | 0 kW                           |
| RATED PERMANENT<br>CURRENT (IU)                       | 160 A                          |
| RATED UNINTERRUPTED<br>CURRENT (IU)                   | 160 A                          |
| CONDITIONED RATED<br>SHORT-CIRCUIT CURRENT<br>IQ      | 100 kA                         |
| WITH ERROR<br>PROTECTION                              | Yes                            |
| NUMBER OF POLES                                       | Three-pole                     |
| RATED OPERATION<br>POWER AT AC-23, 400 V              | 0 kW                           |
| RATED SHORT-TIME<br>WITHSTAND CURRENT<br>(ICW)        | 0 kA                           |
| ELECTRICAL<br>CONNECTION TYPE OF<br>MAIN CIRCUIT      | Screw connection               |
| ACTUATOR POSITION                                     | Front side                     |
| ACTUATOR TYPE                                         | Long turning handle            |
| SUITABLE FOR                                          | Front mounting                 |
| RATED CONDITIONAL<br>SHORT-CIRCUIT CURRENT<br>(IQ)    | 100 kA                         |
| SUITABLE FOR FUSES                                    | NH00                           |
| CABLE ENTRY TYPE                                      | Side                           |
| DEGREE OF PROTECTION<br>(FRONT SIDE)                  | IP40                           |
| POWER RATING AT AC-23,<br>400 V                       | 0 kW                           |
| RATED OPERATING<br>VOLTAGE (UE) AT AC -<br>MAX        | 690 V                          |

